


- 1.CABLE:13 PCS UL CABLE,(26AWG(7/0.16),TINNED AND STRANDED COPPER WIRE
JACKET:PVC,COMPLIANCE ROHS
- 2.CONNECTOR:1 PCS 24+5 DVI WAYS MALE SOLDER TYPE CONNECTOR
INSULATOR:P.B.T.+GLASS FIBER,COLOR:WHITE
CONTACT:COPPER ALLOY,GOLD ,SHELL:BRASS TIN PLATED.
CONNECTOR COMPLIANCE ROHS
- 3.CONNECTOR:1 PCS HDD15 PIN FEMALE SOLDER TYPE CONNECTOR WITH TO NUTS
INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE
CONTACT:COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED
SHELL:STELL,NICKEL PLATED
CONNECTOR COMPLIANCE ROHS
- 4.HOOD:PVC MOLDED TYPE WITH SHIELDED ON INNER
MOLD AND INJECTION OUTER MOLD WITH THUMB SCREW#4-18.5 UNC
MOLDED COLOR:BLACK,MOUDED THUMB SCREW ARE BLACK COLOR
- 5.Fulfill ROHS Guideline
- 6.ELECTRONIC TEST:100% OPEN SHORT+MISS WIRE TEST

PIN OUT

DVI MALE (P1)	WIRE	HDD15 JACK (J1)
6	=====	15
7	=====	12
8	=====	14
15	=====	5
15	=====	10
14	=====	9
16	=====	9
C1	=====	1
C5	=====	6
C2	=====	2
C5	=====	7
C3	=====	3
C5	=====	8
C4	=====	13
SHELL	=====	SHELL

PART NO 2263	SHEET NO 1	 THIRD ANGLE PROJECTION SCALE N.T.S DRAWN BY & DATE SIZE A4 CHECKED BY & DATE UNIT <input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH	有得 限 公 司 股 份
TITLE: DVI MALE TO HDD15 FEMALE, BLACK COLOR			
DWN NO D-2263			