

Radeon FreeSync™

Clearer, Smoother Image

With Radeon FreeSync™, gamers can experience seamless, fluid movement throughout hi-res, fast-paced games. Radeon FreeSync™ virtually eliminates screen tearing and stuttering.



Dynamic Action Sync

React Faster to The Action

Minimize input lag with Dynamic Action Sync so you can catch every single moment in real-time.



Black Stabilizer

Enemies Have Nowhere to Hide



OnScreen Control

Easier User Interface


OnScreen Control is simple and intuitive. You can customize your display options with a few simple clicks.



Screen Split



Monitor Setting



*To download latest OnScreen Control, visit LG.com. The picture shown for illustration purpose only.

Wall Mountable

Convenient and Flexible

This monitor gives you the freedom to take it off the desk and hang it on the wall. Liberate your viewing options and save desktop space with this wall-mountable LG monitor.



Wall Mountable



Tilt



[Close](#)

General

Size (Inch / cm)

23.5" / 59.8cm

Panel Type

TN

Colour Gamut (CIE1931)

NTSC 72%

Colour Depth (Num of Colours)

16.7M colors

Pixel Pitch (mm)

0.2745 x 0.2745

Aspect Ratio

16:9

Resolution

1920 x 1080

Brightness (Typ.)

250cd/m²(Typ.) 200cd/m²(Min.)

Contrast Ratio (Original) 1000:1 (Typ), 700:1 (Min.)	(GTG) 1ms (faster)
---	-----------------------

Viewing Angle (CR≥10) 170/160	Surface Treatment Anti glare, 3H
----------------------------------	-------------------------------------

Jack Input / Output

D-Sub Yes (1ea)	HDMI Yes (1ea)
--------------------	-------------------

Headphone Out
Yes

Power

Type Adapter	Input 100-240Vac, 50/60Hz
-----------------	------------------------------

Normal On (typ.) 26.0W (Typ), 30.0W (Max.)	Sleep Mode (Max) Under 0.3W
---	--------------------------------

DC Off (Max)
Under 0.3W

Frequency

D-sub (Max Resolution / Hz) 1920x1080 / 60Hz	HDMI (Max Resolution / Hz) 1920 x 1080/75Hz
---	--

Resolution

PC (D-sub) 1920 x 1080	Digital (DVI-D / HDMI) 1920 x 1080
---------------------------	---------------------------------------

Special Feature

Flicker Safe

Yes

Reader Mode

Yes

Colour weakness

Yes

Super resolution +

Yes

RADEON FreeSync™

Yes

Black Stabilizer

Yes

Dynamic Action Sync

Yes

Crosshair

Yes

Smart Energy saving

Yes

OnScreen Control (OSC)

Yes

Stand

Tilt (Angle)

Yes

Wall Mount(mm)

75 x 75

Dimension (W*D*H, mm)

Set (with Stand)

555 x 181.9 x 420.5

Set (without Stand)

555 x 38.4 x 330.9

Box

688 x 124 x 390

Wall Mount size (mm)

75 x 75

Weight (Kg)

Set (with Stand)

2.8

Set (without Stand)

2.5

Box

4.1
