

TWYST™

SHAPING LIGHT LIKE NEVER BEFORE

First in the industry, with our patented design, the TWYST™ is a flashlight, work light and lantern - all in one! Leave the lantern, the work light and the flashlight at home! You only need the TWYST™ to cover all your bases.

DESIGN

- Dimmable beam
- TWYST™ Bezel reveals C·O·B LED
- Anodized aircraft-grade aluminum; water and impact-resistant
- Retractable base stabilizers provide convenient hands-free lighting on uneven surfaces
- Powerful magnetic base

OPERATION

- Side-positioned ON/OFF button



LIGHT MODES

FLASHLIGHT: 270 Lumens	4 Hours / 233 Meters
WORK LIGHT: 110 Lumens	13.5 Hours / 15 Meters
LANTERN: 250 Lumens	4 Hours / 15 Meters

TWYST™ SPECIFICATIONS

WEIGHT	0.85 lbs.
LENGTH	7.5" (Compacted) / 7.875" (Extended)
DIAMETER	2" (Head) / 1.25" (Barrel)
BATTERIES	4 AA batteries included
U.S. PATENTS	International patents pending



UPC CODE	ITEM	DESCRIPTION	MSRP
645397930310	6301	iPROTEC™ TWYST™ Flashlight, Work Light & Lantern	49.99