

# 09 02 240 T

## Lineman's Pliers with tether attachment point

American style




- Improved version
- Now requires 50% less effort compared with conventional combination pliers due to an optimised transmission ratio
- Solid construction for heaviest strain; universally applicable
- Ergonomically optimised handle shape for firm contact to the hand and fatigue reducing operation
- Particularly effective cross-hatched knurled gripping zone in the jaws - for strong gripping and pulling
- Additional gripping zone below the joint for powerful leverage and pressing performance
- With cutting edges for soft and hard wire
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Vanadium electric steel, forged, multi stage oil-hardened
- Pliers with tether attachment point for mounting a fall protection

<b>Article No.</b>	09 02 240 T
<b>EAN</b>	4003773079941
<b>Pliers</b>	black atramentized
<b>Head</b>	polished
<b>Handles</b>	with multi-component grips, with integrated tether attachment point for a tool tether
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	4,6
<b>Cutting capacities hard wire (diameter) Ø mm</b>	3,0
<b>Length mm</b>	240
<b>Net weight g</b>	463



Gripping zone below the joint for powerful leverage



Cross-hatched, knurled gripping zone for firm gripping and pulling, e. g. for fence construction



Long cutting edges for cutting flat cables

technical change and errors excepted