


# 12 11 180


## Insulation Stripper with adapted blades



- With replaceable blades for 4 or 6 different conductor cross-sections
- Leave wire undamaged thanks to precision-ground blade shapes, even multi-stranded conductors are stripped gently
- During stripping, the wire is held firmly by clamping jaws
- With length stop for constant stripping length during repetitive work
- A spring leads the stripper back to the starting position
- Pliers body: aluminium
- Blade: special tool steel, oil-hardened



<b>Article No.</b>	12 11 180
<b>EAN</b>	4003773000792
<b>Pliers</b>	black lacquered
<b>Handles</b>	with plastic grips
<b>Stripping capacities (diameter) Ø mm</b>	0,5 / 1,2 / 1,6 / 2,0
<b>Length mm</b>	180
<b>Net weight g</b>	368



technical change and errors excepted



### Spare Parts

Article No.	EAN	
12 19 180	4003773022145	1 pair of spare blades for 12 11 180 with adapted blades
12 19 180 04	4003773052876	Insulation support (4) for 12 11/21 ..
12 19 180 06	4003773052890	Guide plate (6) for 12 11/21 ..
12 19 180 07	4003773052906	Joining bar (7) for 12 11/21 ..
12 19 180 08	4003773052913	Bolt (8) for 12 11/21 ..
12 19 180 09	4003773052920	Screw (9) for 12 11/21 ..
12 19 180 10	4003773052937	Torsion spring (10) for 12 11/21 ..
12 19 180 11	4003773052944	Washer (11) for 12 11/21 ..
12 19 180 12	4003773052951	for 12 11/21 ..
12 19 180 13	4003773052968	Opening spring (13) for 12 11/21 ..
12 19 180 14	4003773052975	Joint screw (14) for 12 11/21 ..
12 19 180 15	4003773052982	Handle sleeve (15) for 12 11/21 ..
12 19 180 16	4003773052999	Intermediate stop lever (16) for 12 11/21 ..

12 19 180 17	4003773053002	Bolt for intermediate stop lever (17) for 12 11/21 ..
12 19 180 22	4003773053057	for 12 11/21 ..
12 19 180 23	4003773053064	Adjusting and fastening screws (20-21) for 12 11/21 ..