



12 49 02

1 pair of spare clamping jaws for 12 40 200




Mode of operation of straight cutters


An incision is made in the red area only.

Not suitable for highly-flexible or armoured insulation materials or for multi-layered insulation.


Article No.	12 49 02
EAN	4003773026686
Stripping capacities in square millimetres mm ²	
Length stop mm	
AWG	
	1
Length mm	
Net weight g	2



12 40 200: Adjustable length stop



Wire cutter for multiple stranded wire cables up to 10.0 mm²



12 40 200: Precise stripping prevents damage to the conductor

technical change and errors excepted



Products

No.	EAN	
12 40 200	4003773026662	