


13 05 160 T

Electricians' Pliers with tether attachment point




- The ideal pliers for cable work
- For gripping and bending wire
- For cutting soft, medium and hard wire
- Precision cutting edges additionally induction hardened, cutting edge hardness approx. 60 HRC
- With precision stripping holes
- For crimping end sleeves (ferrules)
- Vanadium electric steel, forged, multi stage oil-hardened
- Pliers with tether attachment point for mounting a fall protection


Article No.	13 05 160 T
EAN	4003773079965
Pliers	chrome plated
Head	
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Cutting capacities medium hard wire (diameter) Ø mm	2,5
Cutting capacities hard wire (diameter) Ø mm	1,6
Stripping capacities in square millimetres mm²	0,5 - 0,75 / 1,5 / 2,5
Length mm	160
Net weight g	142




Gripping



Cutting



Stripping



Crimping 0.5 to 2.5 mm²

technical change and errors excepted