

13 42 165

Stripping Pliers



- For time-saving stripping of all round sheathed and damp-proof installation cables (e.g. NYM cable)
- Simplified access especially into deep mounted junction boxes thanks to slim head design and optimally angled cable sheath cutter
- Strip cables easily and without damage thanks to circular cutting edge with depth limiter
- Suitable for universal use: precision wire stripping holes for conductors from 1.5 and 2.5 mm²
- With side cutters for cutting and trimming conductors, wires, small screws and nails
- All cutters additionally induction hardened to approx. 61 HRC for high wear resistance
- 30 % lighter than comparable pliers
- Vanadium electric steel, forged, multi stage oil-hardened

Article No.	13 42 165
EAN	4003773079675
Head	polished
Handles	with multi-component grips
Pliers	black atramentized
Cutting capacities medium hard wire (diameter) Ø mm	3,2
Cutting capacities hard wire (diameter) Ø mm	2,2
Cable stripping values (diameter) Ø mm	8 - 13
Stripping capacities in square millimetres mm²	0,75 - 1,5 / 2,5
Length mm	165
Net weight g	176



Cutting cable up to Ø 13 mm



Cutting when shortening single conductors



wire stripping holes for 1.5 and 2.5 mm² conductors

technical change and errors excepted