

13 66 180 T

KNIPEX StriX Insulation Stripper with Cable Shears with tether attachment point



- For single, multiple and fine stranded conductors with plastic or rubber insulation up to 5.0 mm dia. or 10 mm² cable cross-section
- Increments in the jaw provide a visual orientation aid for stripping consistent lengths (11 mm and 16 mm)
- Easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- Shear blade for cutting copper and aluminium cable up to Ø 15 mm (5 x 2.5 mm²)
- Slim dimensions for easy access
- Bolted joint: precise, zero backlash operation of pliers
- High-grade special tool steel, forged, multi stage oil-hardened
- Pliers with integrated, insulated tether attachment point for a tool tether

Article No.	13 66 180 T
EAN	4003773081906
Pliers	chrome plated
Head	
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	15
Cutting capacity copper cable, multiple-stranded mm²	50
Stripping capacities in square millimetres mm²	10
Stripping capacities (diameter) Ø mm	5
AWG	8
Length mm	180
Net weight g	212

technical change and errors excepted