

# 25 05 140


## Snipe Nose Side Cutting Pliers (Radio Pliers)



- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction hardened, cutting edge hardness approx. 61 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



<b>Article No.</b>	25 05 140
<b>EAN</b>	4003773035015
<b>Pliers</b>	chrome plated
<b>Handles</b>	with multi-component grips
<b>Style</b>	0
<b>Head</b>	
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	2,5
<b>Cutting capacities hard wire (diameter) Ø mm</b>	1,6
<b>T1 mm</b>	8,0
<b>W3 mm</b>	15,0
<b>W4 mm</b>	2,5
<b>T2 mm</b>	2,0
<b>L3 mm</b>	42,0
<b>Length mm</b>	140
<b>Net weight g</b>	111



technical change and errors excepted

