

# 26 16 200


## Snipe Nose Side Cutting Pliers (Stork Beak Pliers)



- High loadable, elastic precision points
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for medium hard wire max. dia. 3.2 mm and hard wire max. dia. 2.2 mm
- Cutting edges additionally induction hardened, cutting edge hardness approx. 61 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



<b>Article No.</b>	26 16 200
<b>EAN</b>	4003773022831
<b>Pliers</b>	chrome plated
<b>Handles</b>	insulated with multi-component grips, VDE-tested
<b>Head</b>	
<b>Style</b>	1
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	3,2
<b>Cutting capacities hard wire (diameter) Ø mm</b>	2,2
<b>T1 mm</b>	9,5
<b>W3 mm</b>	18,0
<b>W4 mm</b>	3,0
<b>T2 mm</b>	2,5
<b>L3 mm</b>	73,0
<b>Nominal size</b>	200 mm
<b>Length mm</b>	200
<b>Net weight g</b>	206



technical change and errors excepted

