

73 06 160

KNIPEX X-Cut® Compact Diagonal Cutter



- Compact and 25 % less weight. Powerful and precise
- Cuts finest strands as well as multi-core cables and piano wires
- Box-joint design: highest stability with low weight
- Doubly supported joint axis for heaviest duty
- High cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- 40% less force required compared with standard diagonal cutters of the same length
- Large opening width for thicker cables
- Cuts precisely, even through fine copper wires
- Compact, low-weight construction
- Universally usable, in the assembly, maintenance and production
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened

40% less force required compared with standard diagonal cutters of the same length

with double mounted hinged joint

Article No.	73 06 160
EAN	4003773075141
Head	
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacities medium hard wire (diameter) Ø mm	3,8
Cutting capacities hard wire (diameter) Ø mm	2,7
Cutting capacities piano wire (diameter) Ø mm	2,2
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	12,0
Cutting capacities soft wire (diameter) Ø mm	4,8
Length mm	160
Length mm	160
Net weight g	175



technical change and errors excepted

