

# 74 02 160

## High Leverage Diagonal Cutter



- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened




### 20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.

<b>Article No.</b>	74 02 160
<b>EAN</b>	4003773023081
<b>Pliers</b>	black atramentized
<b>Head</b>	polished
<b>Handles</b>	with multi-component grips
<b>Style</b>	0
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	3,4
<b>Cutting capacities hard wire (diameter) Ø mm</b>	2,5
<b>Cutting capacities piano wire (diameter) Ø mm</b>	2,0
<b>Length mm</b>	160
<b>Net weight g</b>	209



*technical change and errors excepted*

