

74 12 180

High Leverage Diagonal Cutter



- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
 - Style: with opening spring; to be activated if required



20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.

Article No.	74 12 180
EAN	4003773060192
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Style	1
Cutting capacities medium hard wire (diameter) Ø mm	3,8
Cutting capacities hard wire (diameter) Ø mm	2,7
Cutting capacities piano wire (diameter) Ø mm	2,2
Length mm	180
Net weight g	273



74 12: opening spring in deactivated position



74 12: just gentle sliding with your thumb will activate the opening spring

technical change and errors excepted

