


# 77 52 115 ESD

## Electronics Diagonal Cutter ESD



- For fine cutting work, e.g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened
- With two-colour dual component grips, black/grey
- High-grade special tool steel, forged, multi stage oil-hardened
- Pointed, flat head, with small bevel
- Cutting edge hardness approx. 60 HRC




### ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

Article No.	77 52 115 ESD
EAN	4003773025139
Head	mirror polished
Handles	with multi-component grips
Style	5
Cutting capacities medium hard wire (diameter) Ø mm	0,8
Cutting capacities hard wire (diameter) Ø mm	0,5
Cutting capacities soft wire (diameter) Ø mm	0,3 - 1,0
B mm	13,0
D mm	7,0
A mm	11
Length mm	115
Net weight g	79



technical change and errors excepted

