


78 23 125

Electronic *Super Knips*®



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Ground, very sharp cutting edges without bevel
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Precision shaped tips cut wires resting on a board from 0.2 mm dia.
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter
- Cutting edge hardness approx. 54 HRC
- INOX - tool steel

Article No.	78 23 125
EAN	4003773043096
Head	polished
Handles	with multi-component grips
Style	2
Pliers	
Cutting capacities medium hard wire (diameter) Ø mm	0,6
Cutting capacities soft wire (diameter) Ø mm	0,2 - 1,0
B mm	5,5
D mm	7,5
A mm	13,5
Dimensions angle °	60
Length mm	125
Net weight g	55



technical change and errors excepted

