


# 78 91 125

## Electronic Super Knips®



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Ground, very sharp cutting edges without bevel
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Precision shaped tips cut wires resting on a board from 0.2 mm dia.
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter
- Precision ground cutting edges with very small bevel suitable also for hard wire
- With lead catcher - no uncontrolled loss of cut wire ends
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Special tool steel, burnished

<b>Article No.</b>	78 91 125
<b>EAN</b>	4003773065081
<b>Pliers</b>	burnished
<b>Handles</b>	with multi-component grips
<b>Style</b>	9
<b>Head</b>	
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	1,2
<b>Cutting capacities hard wire (diameter) Ø mm</b>	0,6
<b>Cutting capacities soft wire (diameter) Ø mm</b>	0,2 - 1,6
<b>D mm</b>	7,5
<b>B mm</b>	9,0
<b>A mm</b>	13,5
<b>Length mm</b>	125
<b>Net weight g</b>	57



technical change and errors excepted

