




# 86 07 250

## Pliers Wrench insulated



- Pliers and a wrench in a single tool
- Also excellent for gripping, holding, pressing and bending workpieces
- Zero backlash jaw pressure prevents damage to edges of sensitive and soft nuts (Cu)
- With scale for presetting the opening width apart from the workpiece
- No unintentional shift of the gripping jaws and no slipping of the joint
- Parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened

<b>Article No.</b>	86 07 250
<b>EAN</b>	4003773065067
<b>Pliers</b>	chrome plated
<b>Handles</b>	with dipped insulation, VDE-tested
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>B2 mm</b>	8
<b>B3 mm</b>	14
<b>B1 mm</b>	8,0
<b>Adjustment positions</b>	17
<b>Capacities for nuts Inch</b>	1 3/4
<b>Capacities for nuts mm</b>	46
<b>Length mm</b>	250
<b>Net weight g</b>	615



Scale for setting the opening width, apart from the workpiece

technical change and errors excepted

