

89 01 250

Water Pump Pliers with groove joint



- Easy, convenient engagement in 5 different positions due to milled tongue
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Non-slip joint
- Jaw profile designed to fit screws and nuts
- Joint design reduces strain of the centre bolt, hence no wear on pivot
- Guard prevents operators' fingers being pinched
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC for tool length 250 mm: high wear resistance and stable gripping
- Chrome vanadium electric steel, forged, multi stage oil-hardened

| | |
|----------------------------------------------|--------------------|
| Article No. | 89 01 250 |
| EAN | 4003773013334 |
| Pliers | black atramentized |
| Head | polished |
| Handles | plastic coated |
| Capacity for pipes, inches (diameter) Ø Inch | 1 5/16 |
| Capacities for nuts mm | 36 |
| Capacities for pipes (diameter) Ø mm | 34 |
| Length mm | 250 |
| Net weight g | 340 |

technical change and errors excepted



Spare Parts

| Article No. | EAN | |
|--------------|---------------|-----------------------------|
| 89 09 250 01 | 4003773053576 | Joint screw for 89 01 250 |
| 89 09 250 02 | 4003773053583 | Hexagonal nut for 89 01 250 |