

95 12 165 T

Cable Shears with tether attachment point




- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Clean and smooth cut without crushing and deformation
- Not suitable for steel wire and hard drawn copper conductors
- Precision ground, hardened blades
- Easy cutting with one-hand operation
- With guard
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened



- Pliers with tether attachment point for mounting a fall protection

Article No.	95 12 165 T
EAN	4003773080190
Tool	burnished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Style	1
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	15
Cutting capacity copper cable, multiple-stranded mm²	50
AWG	1/0
Length mm	165
Net weight g	255



Cut performed with a Diagonal Cutter: high effort required, inaccurate cut, considerable deforming and crushing of the cable



Cut performed with a Cable Shear: easy, clean cut without any deformation of the cable

technical change and errors excepted