

95 36 250

Cable Cutter ratchet action



PATENTED



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and wire ropes
- Precision ground, hardened blades
- Clean and smooth cut without crushing and deformation
- One-hand operation using ratchet principle
- Little handforce required due to very high transmission ratio
- Two-stage ratchet drive for easy cutting
- Simple handling as a result of low weight and compact design - can be used even in confined areas
- Guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened

Article No.	95 36 250
EAN	4003773026884
Tool	black lacquered
Handles	insulated with multi-component grips, VDE-tested
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	32
Cutting capacity copper cable, multiple-stranded mm²	240
MCM	500
Length mm	250
Net weight g	652



Ratchet principle and two-stage ratchet drive for easier cutting

technical change and errors excepted



Spare Parts

Article No.	EAN	
95 39 250	4003773022244	Movable spare blade for 95 31 250 / 95 36 250 ratchet action