

97 33 01

KNIPEX MultiCrimp® crimping pliers with changer magazine and 3 crimping dies



- Just one tool for the most common crimping applications
- Crimping dies changed quickly and easily without any additional tool
- Sorted and protected storage of the interchangeable dies in a round magazine
- Comfortable, powerful crimping pliers in professional quality
- Same reliable crimping results as with fixed crimping dies
- Repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Chrome vanadium electric steel in special quality, oil-hardened
- Round magazine: plastic, fibreglass-reinforced



Compact, inexpensive and light-weight crimping pliers for fitting and repairs. The electrician needs only one tool now instead of five as before.

Article No.	97 33 01
EAN	4003773066927
Pliers	burnished
Handles	with multi-component grips
Applications	non-insulated open plug type connectors (plug width 4.8 + 6.3 mm)
Capacity in square millimetres mm²	0,5 - 6,0
Number of crimping positions	3
AWG	20 - 10
Length mm	250
Net weight g	770



Changing position: service lever opens out for parallel jaw positioning



Changing the crimping dies: unlock the magazine position, take out the set of dies which the pliers have been pushed on



Fold in the service lever and press the pliers - ready for use again



Magazine for crimping dies can be carried on a belt



Clearly visible marking on the crimping dies with pictograms

technical change and errors excepted



Accessories

Article No.	EAN	
97 39 05	4003773070078	Crimping dies for non-insulated open plug type connectors (plug width 4.8 + 6.3 mm)
97 39 06	4003773070085	Crimping dies for insulated terminals, plug connectors and butt connectors
97 39 08	4003773070092	Crimping dies for insulated and non-insulated end sleeves (ferrules)
97 39 09	4003773077763	Crimping dies for insulated and non-insulated end sleeves (ferrules)

97 39 13	4003773070108	Crimping dies for non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267
97 39 30	4003773070115	Crimping dies for compression joints according to DIN 46267
97 39 90	4003773070061	Changer Magazine empty