

97 52 10

Crimping Pliers also for two-hand operation




- For solder-free electrical connections
- The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers
- Repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Two-hand operation for easy crimping of large conductor diameters
- Easy handling as a result of well balanced centre of gravity, angled head and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened

| | |
|-------------------------------------|--------------------------------|
| Article No. | 97 52 10 |
| EAN | 4003773023678 |
| Pliers | burnished |
| Handles | with non-slip plastic grips |
| Applications | Coax-, BNC- and TNC-connectors |
| Cable type | RG 58 / 59 / 62 / 71 / 223 |
| Number of crimping positions | 3 |
| Length mm | 250 |
| Net weight g | 577 |



First step: move the handle with two fingers only until both jaws touch the connector to be crimped



Second step: now use the whole hand for further crimping procedure



Third step: when greater hand force is required, such as e.g. when crimping insulated connectors 6.0 mm², two-hand operation is possible by the longer handles

technical change and errors excepted



Spare Parts

| Article No. | EAN | |
|-------------|---------------|-------------------------------|
| 97 59 20 | 4003773053934 | Extension spring for 97 52 xx |
| 97 59 21 | 4003773053941 | Extension spring for 97 52 xx |