

97 52 30

KNIPEX PreciForce® Crimping Pliers



- Repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



For daily crimping applications, the specialist likes crimping pliers that work precisely and reliably. In addition, they should be light, comfortable to use, robust and reasonably priced: PreciForce®.

| | |
|--|---|
| Article No. | 97 52 30 |
| EAN | 4003773051855 |
| Pliers | burnished |
| Handles | with multi-component grips |
| Applications | non-insulated crimp connectors in accordance with DIN 46267 |
| Capacity in square millimetres mm² | 1,5 - 4,0 |
| Number of crimping positions | 3 |
| AWG | 15 - 11 |
| Length mm | 220 |
| Net weight g | 477 |

technical change and errors excepted



Spare Parts

| Article No. | EAN | |
|-------------|---------------|-------------------------------|
| 97 59 20 | 4003773053934 | Extension spring for 97 52 xx |
| 97 59 21 | 4003773053941 | Extension spring for 97 52 xx |