

GKM681R

2.4GHz Wireless Compact Keyboard with Optical Trackball and Scroll Wheel




IOGEAR's innovative new 2.4GHz Wireless Compact Keyboard with Optical Trackball and Scroll Wheel gives you the comfort and freedom of up to 33 feet of wireless connectivity between you and your videos, photos, movies and online content. The ergonomic design enhances the user experience by making the way you type, navigate and interact with your content easier and more natural. It serves as an ideal productivity solution for PC to TV setups, as well as interaction with game consoles accessibility to multimedia and online content; driving your content how you want it and when you want it from the comfort of your couch.

Great for:

- HTPC (Home Theater PC's) setups
- Media server's / Computers / Laptops
- Latest game consoles such as, PS3 and XBOX
- PC-to-TV solution
- 2.4GHz Wireless Compact Keyboard with built-in optical trackball, left / right buttons and scroll wheel
- Ideal convenience to drive the PC to TV content you want, when and how you want it; all wirelessly!
- Provides an intuitive way of interaction with game consoles' accessibility to multimedia and online content
- 2.4GHz technology offers greater wireless range up to 33 feet away from your home theater PC / Computer or Laptop
- Conveniently placed buttons and optical trackball for exceptional and precise singlehanded navigation
- 16 multimedia hotkeys for quick access from Internet Browser, My Computer and Windows Media Player track and volume control
- USB wireless dongle can be stored in the bottom of the keyboard for safe storage
- The perfect solution for Digital Living Rooms / PC-to-TV





Requirements

Package Contents

Computer / Device*

- 1 USB port

- 1 x 2.4GHz Wireless Keyboard
- 1 x USB RF Receiver
- 2 x AAA Alkaline Battery
- 1 x Quick Start Guide
- 1 x Warranty Card

Operating System

- Windows® 10, Windows® 8.1 (32-bit / 64-bit), Windows® 8 (32-bit / 64-bit), Windows® 7 (32-bit / 64-bit), Windows Vista® (32-bit / 64-bit), Windows XP®
- Mac OS X v10.3.9 or later**

*Device must support USB HID keyboard device and USB HID-compliant mouse in order to have the keyboard and mouse function correctly respectively.

**Some Mac special keys may not work.

Specifications

Function		GKM681R	Dimensions		GKM681R
Radio Frequency		2.4GHz (2.401-2.483)	Unit Dimensions		
Connectors			Width		10.25"
USB		RF Receiver with HID support	Height		4.5"
Operating Range		Up to 10m (33ft)	Depth		1.25"
Resolution		800 DPI Trackball Resolution	Unit Package Dimensions		
Battery Type		2 x AAA Alkaline Battery	Width		12.25"
Environment			Height		6"
Operation Temperature		0-45C	Depth		2"
Storage Temperature		-20-60C	Master Carton		
Humidity		20-90%	Width		13"
Housing			Height		7"
Case		Plastic	Depth		12.5"
Power			Master Carton Qty.		6
Voltage		Keyboard: 3V, USB: 5V	Weight		
Power Management		Green LED low battery indicator	Master Carton Wt.		6.92 LB
Power Mode		Automatic standby mode after 5 mins inactivity	Unit Pack Wt.		1 LB
Power Consumption		100 hours continuous usage	Unit Wt.		0.7 LB
Warranty		3-Year			