

# PRAKTICA

## Luxmedia Z35

35X Optical Zoom  
25mm Wide

HD Video  
1080p

O.I.S  
Image Stabilization

The Luxmedia Z35 Bridge Camera gives you the flexibility of a DSLR with the ease of a point and shoot. With a powerful 35x optical zoom, you can capture moments from far and wide.

Never worry about low light again, whether it's day or night, choose from 26 creative modes to take the perfect photograph at the touch of a button. You'll be sure to impress with every shot.

Available in Black.



### Key Features

- 16MP CMOS Sensor
- 35x Optical Zoom Lens
- 1080p Video Recording
- Optical Image Stabilization
- 3.0 inch LCD Screen
- Built in Flash, Microphone & Speaker
- 26 fun & creative modes
- Storage: Up to 64 SDXC Card
- Accessories Included: USB Cable & Adapter, Wrist Strap, Lens Cover, Li-ion Battery, Quick Start Guide

### Specification

Black: Z35-BK

Image Resolution	16 Megapixels	Microphone/Speaker	Built-in
Image Sensor	1/2.3" CMOS	ISO Sensitivity	Up to 6400
Resolution	4768x3516	USB	USB(HS) Type-B Micro Connector
Focal Length	4.5(W) - 157(T)mm	Power Source	Lithium Ion NP-120 Battery
Photo Format	JPEG	Dimensions	124.5x84.3x92mm
Video Format	MP4 (.MOV)	Weight	496g
Video Resolution	1080p60 (FHD)		

# PRAKTICA

## Luxmedia Z35




Image Sensor	1/2.3" CMOS
Effective Pixels	4672x3500 (16.35M)
Total Pixels	4768x3516 (16.76 M)
Aspect Ratios	4:3
Focal Length	4.5(W) - 157(T)mm (35mm equiv. 25 - 875mm)
Zoom	35x Optical, 2x Digital
Maximum f/number	f/3.0-f/5.9
Image Stabilization	Optical Image Stabilization
Screen	3.0" (7.7cm)/460,000 dots/RGB delta
Auto Focus Area	Face Tracking/ Wide/ Center/ Tracking AF
Auto Focus Modes	Auto/ Macro/ Super Macro/ Infinity
Exposure Metering	Multi / Centre / Spot
Exposure Bracketing	Off / ±0.3 / ±0.7 / ±1.0
ISO Sensitivity	AUTO, 125, 200, 400, 800, 1600, 3200, 6400
Shutter Speed	Auto:1 – 1/2000 sec/ Night: 1/15 - 1/2000 sec/ Fireworks: 4 secs
White Balance Settings	Auto / Daylight / Cloudy / Tungsten / Fluorescent_1 / Fluorescent_2 / Custom
Strobe Flash	Wide 0.5~7.5m @ ISOAuto/Tele 1.5~3.8m @ISOAuto
Flash Recharging Time	Full 4.2V recharge ≤6s, low 3.5V recharge ≤10s
Mode Dial	Intelligent Scene/Scene Mode/Panorama/Art Effect/Manual Exposure/Aperture Priority/Shutter Priority/Program
Intelligent Scene Modes	Other Subjects/Portrait/Landscape/Macro/Backlight/Backlight Portrait/ Night Scene/ Night Portrait
Panorama	120°/180°/360°
Scene Mode	Portrait/Landscape/Sunset/Dawn/Backlight/Kids/Night Scene/Close-up/Fireworks/Beach/Snow/Sports/Party/ Candlelight/Night Portrait/Soft Skin/Food/Moon/Background Blur/Love Portrait/Self Portrait/Smile Shutter/ HDR/Timelapse/Continuous/GIF Capture
Time Lapse	30 secs/1 min/5 mins/10 mins/30 mins/60 mins
Movie Resolution	1920x1080@60fps (FHD)/1920x1080@30fps/1280x720@30fps (HD)/640x480@30fps (VGA)
Movie Length	Up to 29min
Still Image Format	JPEG
Movie Format	AVI (MJPEG)
Microphone	Built-in
Playback Zoom	Approx. 1x – 12x
Self Timer	Off / 10 sec. / 2 sec. / Double
Menu Languages	English / French / Spanish / German / Italian / Russian / Portuguese / Brazil Portuguese / Dutch / Turkish / Polish / Hungarian /Romanian / Czech / Bulgarian / Croatian / Slovak /Slovenian / Greek / Swedish / Norwegian / Finnish / Danish / Arabic / Indonesia /Malay / Thai / Japanese / Korean / S. Chinese / T. Chinese
Recording Media	SD (up to 4GB )/SDHC (up to 32GB) /SDXC (up to 64GB)
Operating System	Mac OS 10.4 ~10.10 / Windows Vista, 7, 8, 10
Power	Rechargeable Lithium Ion Battery NP-120 3.7V, 1700mAh, USB rechargeable
Battery Life	Approx. 400 shots
Accessories Included	USB charging cable, wrist strap, li-ion battery, lens cover, quick start guide
Operating Temperature	0 – 40 °C
Operating Humidity	≤90% Humidity
Dimensions (WxHxD)	124.5 x 84.3 x 92 mm
Weight	Approx. 496g