

# KODAK PIXPRO

## DIGITAL CAMERAS



## AZ652 ASTRO ZOOM

Get ready to harness the boundless power of the brand new KODAK PIXPRO AZ652 Astro Zoom bridge camera that offers astounding 65X optical zoom and so much more. With a top-notch 20 megapixel BSI CMOS sensor, 5fps multi-burst, 24mm wide angle lens and large 3" articulating LCD, photos and HD videos are crystal clear. The result is amazing, razor sharp detail with every shot. Share your moments instantly with your friends and family via Wi-Fi® connectivity for even more flexibility. KODAK PIXPRO Digital Cameras – Tell your story.

### FEATURES:

- 65X Optical Zoom
- 20 MP CMOS
- 5 fps Burst Shooting
- Electronic Viewfinder
- JPEG and RAW Formats
- 3" Articulating LCD (920K Pixels)
- Wi-Fi Connectivity
- Wirelessly Control with Your iOS™/ANDROID™ Device



Available Colors:

● BLACK

**65X**  
OPTICAL  
ZOOM

**24mm**  
WIDE

**20MP**  
CMOS

**1080p**  
FULL HD

**WiFi**  
CERTIFIED

**360°**  
Panorama



# KODAK PIXPRO AZ652

## DIGITAL CAMERA

SPECIFICATIONS	AZ652
Effective Image Sensor Pixels	20.68 Megapixels
Total Image Sensor Pixels	21.14 Megapixels [1/2.3" BSI CMOS]
Lens	
Focal Length [35mm film equivalent]	4.3 mm (Wide) — 279.5 mm (Tele) [24 mm (Wide) — 1560 mm (Tele)]
F number	F2.9 (Wide) — F6.7 (Tele)
Lens Construction	14 groups 18 elements
Compatible Filter Diameter	Ø52mm
Optical Zoom	65x
Focusing Range	Normal: (Wide) 50 cm — ∞, (Tele) 250 cm — ∞ Macro: 1 cm — ∞ (Wide Only)
Electronic Viewfinder	Yes (-3 ~ +1 diopter)
Anti-Handshake	OIS (Optical Image Stabilization)
Digital Zoom	4x Digital Zoom (Combined Zoom: 260x)
Number of Recording Pixels Still Image	(4:3) 20MP: 5184x3888, 10MP: 3648x2736, 5MP: 2592x1944, 3MP: 2048x1536, 0.3MP: 640x480, (3:2) 18MP: 5184x3456, (16:9) 15MP: 5120x2880, 2MP: 1920x1080
Movie	1920x1080: 30fps, 1280x720: 60fps / 30fps, 640x480: 30fps, High-Speed Movie 640x360: 120fps
Image Compression	Best, Fine, Normal
DCF, DPOF (Ver1.1) Support	Yes
File Format	
Still Image	JPEG (Best, Fine), RAW, RAW + JPEG (Best)
Movie	MOV [Image: H.264, Audio: Linear PCM (Stereo)]
Shooting Modes	Auto, P, S, A, M, Face Beautifier, Wi-Fi, SCN, Movie, CS
SCN Modes	ASCN, Panorama, Children, Portrait, Night Portrait, Handheld Night, Landscape, Sport, Sunset, Fireworks, Snow, Party, Pet
Photo Touch-up	Red-Eye Removal, Skin Soften, Eye Brightening, Eye Enlargement
Detection Features	Face, Smile, Blink, Cat, Dog
HDR	Yes
Panorama	Up to 360°
LCD Display	3.0 inch (920K Pixels), Articulating Screen (max. 180° upward / 90° downward)
ISO Sensitivity	Auto, ISO 100/200/400/800/1600/3200
AF Method	Single AF, Continuous AF, Object Tracking, Manual Focus
Focusing Area Selection	Single Area, 25-area, Face Detection, Manual
Exposure Metering Method	Artificial Intelligence AE (AiAE), Center-Weighted Average, Spot (Fixed to Centre of Frame), Face AE
Exposure Control Method	Program AE (AE-Lock Available), Aperture Priority AE, Shutter Priority AE
Exposure Compensation	+/- 3EV in 1/3 Step Increments
Shutter Speed	1/2000 - 30 Seconds
Continuous Shooting	Approx. 5 fps (Full Resolution)
Playback Modes	Single, Index (9/16 Thumbnails) Slide Show, Date, Burst Shooting, Zoom (Approx. x2 - x8)
White Balance Control	Auto (AWB), Daylight, Cloudy, Fluorescent, Fluorescent CWF, Incandescent, Manual, Color Temperature Setting (1,900K ~ 10,000K)
Flash	
Flash Method	Pop-up (Auto)
Flash Modes	Auto, Red-Eye Reduction, Fill Flash, Force Off, Slow Synchro, Red-Eye Reduction + Slow Synchro
Shooting Range	(Wide) Approx. 0.5 m - 8.5 m (ISO800); (Tele) Approx. 2.5 m - 3.8 m (ISO800)
Recording Media	Internal Memory: Approx. 15MB SD/SDHC/SDXC Card (Up to 128GB Support) [MMC Card not supported] (Use Class 4 Card or better)
Other Features	Wi-Fi (802.11 b/g/n), Remote Control (via iOS/Android Device), Eye-Fi, ExifPrint Support, Multi-Language Support (27 Languages)
Jacks	AV-OUT/USB 2.0 (Micro 5 pin USB), HDMI (Type D)
Power	Rechargeable Li-ion Battery LB-070, 7.4V 1000mAh, In-Camera Charging
Shooting Capability (Battery Performance)	Approx. 400 Shots (Based on CIPA Standards)
Operation Environment	Temperature: 32° - 104°F / 0° - 40°C, Humidity: 0 - 90%
Dimensions (WxHxD)	Approx. 25.9 x 89.0 x 113.6 mm (Based on CIPA Standards)
Weight	Approx. 602g (Body Only)
Supplied Accessories	Rechargeable Li-ion Battery, AC Adapter, USB Cable, Neck Strap, Lens Cap, CD-ROM, Service Card, Quick Start Guide, Warranty Card

## JK Imaging Europe Ltd.

Meridien House, 69-71 Clarendon Road,  
Watford WD17 1DS

© 2017 JK Imaging, Ltd. The Kodak trademark, logo and trade dress are used under license from Eastman Kodak Company.  
All information contained in this document is subject to change without notice.

To learn more about KODAK PIXPRO Digital Cameras:  
visit: [kodakpixpro.com](http://kodakpixpro.com)

