



**40" Full HD LED TV with Freeview T2 HD, DVD Player and USB**

- 40" Full HD widescreen LED TV
- Built-in Freeview T2 HD and Digital Freeview Channels
- Built-in DVD Player
- USB – record digital TV and play media files from other devices
- 3 x HDMI inputs for your external devices and consoles
- Can be wall mounted (200mm x 200mm bracket not included)

	<b>EAN</b>	<b>5060062265224</b>
<b>General Feature</b>	Model No.	C40227FT2
	Panel(60Hz/120Hz/3D)	V400HJ6-PE1 C3(60Hz)
	Panel System	39.5 inch LED Panel (Approx. 102cm)
	Purpose	TV/Monitor Optional
	Aspect Ratio	16:9
	Max. Resolution	1920x1080 Full HD
	Contrast Ratio (Typical)	3500:1 (TYP) by panel
	Brightness(TYP cd/m2)	200nits (TYP) by panel
	Viewing Angle( L/R/U/D )	88/88/88/88 (CR≥10)
	AC Switch	N/A
	Cabinet Color	Piano black
	Wall Mounting Support(Screw Size)	VESA, 200 x 200mm (M5* 10)

<b>Reception</b>	TV System	ATV: PAL BG/DK/1 SECAM BG/DK/L/L DTV:DVB-T & DVB-C, MPEG 2,MP@ML, MPEG 4 ,DVBT2
	TV Band	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	NTSC Playback	N/A
	Number of channel for storing	100 Analog / 400 Digital

<b>Sound</b>	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2 x 8W
	Speaker Frequency range	150-20K Hz
	Speaker Distortion	<=7% Max
	Speaker Impedance	4ohm

<b>Connectors Jack</b>	RF Antenna	1
	HDMI	YES x3 (ver1.4)
	CVBS	YES x1 (Mini Jack)
	PC In	D-sub 15Pin x 1
	Audio In	PC audio x 1 (3.5 Mini Jack) CVBS Audio x 1 (Mini Jack ,Shared with Ypbpr)
	Scart	YES x 1
	YPbPr	YES x 1
	Coax	YES x 1
	Earphone Out	YES x 1 (3.5 Mini Jack)
	USB	YES x 1( Multi Media and PVR Movie: *.mpg, *.dat, *.vob, *.avi, *.ts, *.mov,*.mkv,*.mp4 Music: *.mp3, *.wma, *.m4a, *.aac Photo: *.jpg, *.bmp, *.png)
	CI	YES x 1

<b>DVD</b>	DVD Loader	FORYOU
	DVD Solution	MTK-MTK1389
	DVD/DVD-R/DVD+R/DVD-RW/DVD+RW/CD/MP3/JPEG playback	YES
	DVD Reverse Play	YES
	Skip Forward/Reverse	YES
	DVD Multi-Speed Scan/Slow	YES
	Slot-Load Type Vertical Play DVD Mechanism	YES
	DIV X	\

<b>Other Features</b>	APS	ATV, DVBT, DVBC storage in capture order.
	OSD Language	English / French / German / Italian / Spanish / Portuguese
	Teletext	1000 pages
	EPG (Electronic Program Guide)	7 days (not 7 days from satellite transmissions)
	Automatic Tuning	YES
	Sleep Timer	YES (240min)
	Noise Reduction	YES
	Color Temperature Adjustment	YES
	Picture Mode	Standard / Dynamkic / Mild / User
	Home Mode	YES
	Hotel Mode	YES

<b>Power</b>	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	85W
	Standby Power Consumption	0.4W
	Energy Efficiency Class	A

<b>Accessories</b>	QSG	YES x 1
	Remote Control	YES x 1
	Power Cable	YES x 1
	Warranty	YES
	Battery	1.5V(AAA) x 2

<b>Dimension</b>	Unit Dimension With Stand (W x H x Dmm)	908 x 571 x 257
	Unit Dimension Without Stand (W x H x Dmm)	908 x 526 x 86
	Weight of unit (kg)	7.2
	Carton Dimension Without Stand Assembled (W x H x Dmm)	1020 x 655 x 161