



Einhell Germany AG

Einhell

EXPERT

TE-RO 1255 E

Router

Item No.: 4350490

Ident No.: 11045

Bar Code: 4006825537215

The TE-RO 1255 E router is a high-quality, powerful tool for experts to tackle the most challenging routing jobs in solid wood, plywood and particleboard. The routing depth is easy to preselect using the turret stop and can also be exactly adjusted using the precision depth adjustment facility. A chip shield provided additional protection.

Features

- Depth adjustment with turret stop
- Precision depth adjustment with exact twin-tube guide
- Electronic speed control with powerful motor
- Infinitely adjustable cutting depth
- Clamp Ø8 mm and Ø6 mm
- Parallel stop, compass, copy sleeve
- Spindle lock for easy tool change
- High stability for changing the tool
- Plastic insert protects the workpiece surface
- Chip shield
- Soft grip
- Cable clip



Technical Data

- Mains supply	230 V 50 Hz
- Power	1200 W
- Idle speed	11000 - 30000 min ⁻¹
- Stroke height	55 mm
- Clamping device	6 + 8 mm
- Moulding cutter max.	30 mm

Logistic Data

- Product weight	3.25 kg
- Gross weight single packaging	4.4 kg
- Dimensions single packaging	280 x 221 x 172 mm
- Pieces per export carton	4 Pieces
- Gross weight export carton	18 kg
- Dimensions export carton	590 x 370 x 260 mm
- Container quantity (20"/40"/40"HC)	2052 4284 4772



REVOLVER STOP




FINE ADJUSTMENT



ELECTRONIC
11.000-30.000 min⁻¹




PLASTIC
PROTECTION



CABLE CLIP



selbst
ist der Mann
Das Do-it-yourself-Magazin
PRAXISTEST
TESTSIEGER
Ausgabe 07/2010
www.selbst.de



Ø 6mm + 8mm



FINE
ADJUSTMENT



ELECTRONIC