


Part Number: [0714300013](#)
Status: Active
Overview: Ultra+# VHDCI Interconnects
Description: 0.80mm Pitch Ultra+# VHDCI Receptacle, Right Angle, 68 Circuits, PC Tail Length 2.08mm, Shield with Enhanced Ground Tabs, No Screwlocks

Documents:

3D模型	包装规格 PK-71430-0101 (PDF)
图纸 (PDF)	测试总结 TS-71425-9999 (PDF)
产品规格 PS-71425-9999 (PDF)	RoHS 证书

Agency Certification

一般应用注解	线对板
元件类型	Shield with Enhanced Ground Tabs, No Screwlocks
概述	插座
产品名称	Ultra+# VHDCI Interconnects
类型	SCSI+, VHDCI
UPC	N/A
	800756916514
物理	
衬套颜色	N/A
电路数(已装入的)	68
电路数(最多的)	68
颜色-树脂	黑色
耐用性(插拔次数) - 最多次数	500
阻燃性	94V-0
部件属性	插座
锁定插接部位	是
材料-接合处电镀	金
材料-树脂	高温热塑型塑料
Net Weight	4.315/g
行数	2
方向	直角
PCB 焊脚长度	2.08mm
PCB 定位器	是
PCB 保持力	是
PC厚度: 推荐	1.60mm
包装形式	管状
面板安装式	是
间距-接合界面	0.80mm
间距 - 终端界面	0.80mm
有极性的插配件	是
PCB 极性	是
端口	1
穿孔式表面焊接(SMC)	是
运行温度范围	-55° C to +85° C
终端界面: 类型	穿孔式
防水/防尘	否
线径规格 AWG	N/A
电气	
每触点最大电流	0.5A
屏蔽形式	全屏蔽
屏蔽的	是



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series
[71430 Series](#)

Mates With
[71425 Ultra+# VHDCI Plug Kit](#)

电压 -最大 30V AC (RMS)/DC

焊接处理数据

Duration at Max. Process Temperature (seconds) 040

Lead-freeProcess Capability WAVE

Max. Cycles at Max. Process Temperature 003

Process Temperature max. C 245

材料信息

参考: 图纸编号

包装规格 PK-71430-0101

产品规格 PS-71425-9999

销售用图纸 SD-71430-015, SD-71430-3000

测试总结 TS-71425-9999

This document was generated on 10/19/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION