



NMX All Metal Consumer Units



NMX16

MAIN SWITCH - WITH KNOCKOUTS ALL SIDES

CAT REF	MS RATING	MS WAYS	RCD WAYS	RCD WAYS	TOTAL WAYS	KNOCKOUTS
NMX16	100A	16	-	-	16	All sides
NMX20*	100A	20	-	-	20	All sides

MAIN SWITCH - PLAIN SIDES

CAT REF	MS RATING	MS WAYS	RCD WAYS	RCD WAYS	TOTAL WAYS	KNOCKOUTS
NMX16P	100A	16	-	-	16	Rear only (plain sides)
NMX20P*	100A	20	-	-	20	Rear only (plain sides)

NMX ACCESSORIES

CAT REF	PRODUCT	MODULE
NMXDR2	DIN Rail Insert	2
NMXBB2I	Comb Busbar	21
NMXLDK	Temporary Door Locking Device	-

PATRASSES

CAT REF	PRODUCT
NMXPAT1618*	18 Module Pattress
NMXPAT1622*	22 Module Pattress

* Product available 2018



NMXRS14SL

SPLIT LOAD - WITH KNOCKOUTS ALL SIDES

CAT REF	MS RATING	MS WAYS	RCD WAYS	RCD WAYS	TOTAL WAYS	KNOCKOUTS
NMXRS14SL	100A	5 - 9	9 - 5	-	14	All sides
NMXRS18SL*	100A	7 - 11	11 - 7	-	18	All sides

SPLIT LOAD - PLAIN SIDES

CAT REF	MS RATING	MS WAYS	RCD WAYS	RCD WAYS	TOTAL WAYS	KNOCKOUTS
NMXRS14SLP	100A	5 - 9	9 - 5	-	14	Rear only (plain sides)
NMXRS18SLP*	100A	7 - 11	11 - 7	-	18	Rear only (plain sides)

NMX ACCESSORIES

CAT REF	PRODUCT	MODULE
NMXDR2	DIN Rail Insert	2
NMXBB2I	Comb Busbar	21
NMXLDK	Temporary Door Locking Device	-

PATRASSES

CAT REF	PRODUCT
NMXPAT1618*	18 Module Pattress
NMXPAT1622*	22 Module Pattress

* Product available 2018