

## Han M23 P male-c 0,6mm (0,08–0,34mm<sup>2</sup>) Au



Part number	09 15 600 6191
Specification	Han M23 P male-c 0,6mm (0,08–0,34mm <sup>2</sup> ) Au
HARTING eCatalogue	<a href="https://b2b.harting.com/09156006191">https://b2b.harting.com/09156006191</a>

### Identification

Category	Contacts
Series	Han <sup>®</sup> M23 Power
Type of contact	Crimp contact
Description of the contact	Turned 0.6 mm

### Version

Gender	Male
--------	------

### Technical characteristics

Conductor cross-section	0.08 ... 0.34 mm <sup>2</sup>
Contact resistance	≤3 mΩ
Stripping length	4 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated

### Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

### Commercial data

Packaging size	100
Net weight	0.13 g
Country of origin	Germany
Customs tariff number	85366990