


## A COMPACT SOLUTION FOR MODERN CHALLENGES

17.3" Windows based PC with Dual Core Intel® Mobile Celeron® Processor N3350



1600x900 TN Display



Intel® Celeron® up to 2.4 GHz



Internal Storage



Multitouch Screen



Full USB 3.0 port



7.6V 2500 mAh



- High performance multitasking and energy saving: based on the Dual Core Intel® Mobile Celeron® Processor N3350 and support HDD up to 2TB (slot)
- Working with the screen: a 17.3-inch screen with the support of 10-points touch system allows several people work with this monoblock simultaneously

- Absolute freedom: energy efficient CPU and a powerful battery ensure autonomic work anywhere
- Smart advertising platform: All-in-One combines an interactive screen and built-in camera, so it can recognise the gender and age of the audience ensuring only appropriate and relevant content is displayed

<b>Display</b>	Size: 17.3" Resolution: TN (1600 x 900)
<b>OS</b>	Windows 10 Home
<b>CPU</b>	Dual Core Intel® Mobile Celeron® N3350 up to 2.4GHz
<b>Memory</b>	Built-in: 4GB RAM + 32GB ROM Expandable: slot for microSD™ card up to 128GB HDD slot (up to 2 TB)
<b>Power</b>	7.6V@2500 mAh Li-pol Battery
<b>Camera</b>	2.0MP

<b>Connectivity</b>	BT 4.2, Wi-Fi: 802.11b/g/n USB: 3*full USB 3.0 HDMI: HDMI A port Ethernet: RJ45 port
<b>Dimensions</b>	318 x 214 x 13.8 mm
<b>Weight</b>	2018g
<b>In the box</b>	PC All-in-One, AC Adapter, Video Adapter, Quick Start Guide, Warranty Card