

## Ev-n-Spred 2600A plus




Ev-N-Spred® 3-Hole



The 2600APlus is the closest you can get to a commercial spreader without the cost! The steel "T" handle and solid linkage are features offered on our Commercial & Professional spreaders. Utilizing the EV-N-SPRED® 3-Hole Drop Shut-Off System ensures an even and balanced spread pattern of all granular materials, high flotation 22cm high-flotation tires roll smoothly over rough terrain as well as icy conditions. The 18kg capacity rustproof poly hopper provides a low profile to keep it out of the way in the tightest area.

- 18kg Hopper – rustproof poly construction
- Ev-N-Spred® 3-Hole Drop Shut-Off System
- 45kg Load bearing capacity  
- what the frame will support
- 22cm high-flotation pneumatic tires
- Epoxy powder coated chassis
- Steel "T" bar handle
- Solid linkage rate control
- **Optional** Rain cover - #77000



DMMP Limited, Manor Lane, Peckleton, Leicestershire LE9 7RJ  
Tel: 0845 643 9776 Fax: 0845 644 8861 Email: sales@dmmp.co.uk  
www.dmmp.co.uk