

SPECIFICATION SHEET



Product Code EVS2050P

Product Name Ev-n-Spred 2050P with sidespred control.

Product Description

The 3-Hole Drop Shut-Off System and heavy-duty gearbox ensures an even application of all granular materials with professional results. The rustproof 36kg capacity hopper and 25cm pneumatic stud type tyres bring capacity and smooth operation to the user. Fully assembled, with a folding handle, the 2050P will be ready to go from box in seconds and stores easily.

Product Specifications

- Variable control for flow rate
- Large 36Kg hopper capacity
- 3-Hole Drop Shut-Off System
- 45kg Load bearing capacity - what the frame will support
- Folding handles for easy storage
- 25cm pneumatic stud type tyres on rustproof poly rims
- Epoxy powder coated chassis
- Heavy-duty High Speed Gearbox

Ideal For


Spreading dry, free flowing, regular size material. Ice melt products and fine salt products

Other Information

- *Optional* Rain cover


Part No: 77003

Product



Height x Width x Depth Weight
62.2 cm x 53.3 cm x 44.5 cm 8.6 Kgs

Pallet Qty 18



Height x Width x Depth Weight
1.86 m x 1.33 m x 1.60 m 154 Kgs

DMMP Limited, Manor Lane, Peckleton, Leicestershire. LE9 7RJ
T: 01455 825400 E: sales@dmmp.co.uk W: www.dmmp.co.uk

