

Part Details:-

Part Number	Description
GRM03-KIT-COG-DE-A	0201 CLASS 1 CAPACITOR ASSORTMENT KIT

KIT Contents:-

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
1	GRM0335C1HR10WA01	0603M/0201	COG	50Vdc	0.1pF	±0.05pF	0.33max		20
2	GRM0335C1HR20BA01	0603M/0201	COG	50Vdc	0.2pF	±0.1pF	0.33max		20
3	GRM0335C1HR30BA01	0603M/0201	COG	50Vdc	0.3pF	±0.1pF	0.33max		20
4	GRM0335C1HR40BA01	0603M/0201	COG	50Vdc	0.4pF	±0.1pF	0.33max		20
5	GRM0335C1HR50BA01	0603M/0201	COG	50Vdc	0.5pF	±0.1pF	0.33max		20
6	GRM0335C1HR60BA01	0603M/0201	COG	50Vdc	0.6pF	±0.1pF	0.33max		20
7	GRM0335C1HR70BA01	0603M/0201	COG	50Vdc	0.7pF	±0.1pF	0.33max		20
8	GRM0335C1HR80BA01	0603M/0201	COG	50Vdc	0.8pF	±0.1pF	0.33max		20
9	GRM0335C1HR90BA01	0603M/0201	COG	50Vdc	0.9pF	±0.1pF	0.33max		20
10	GRM0335C1H1R0CA01	0603M/0201	COG	50Vdc	1.0pF	±0.25pF	0.33max		100
11	GRM0335C1H1R1CA01	0603M/0201	COG	50Vdc	1.1pF	±0.25pF	0.33max		20
12	GRM0335C1H1R2CA01	0603M/0201	COG	50Vdc	1.2pF	±0.25pF	0.33max		20
13	GRM0335C1H1R3CA01	0603M/0201	COG	50Vdc	1.3pF	±0.25pF	0.33max		20
14	GRM0335C1H1R4CA01	0603M/0201	COG	50Vdc	1.4pF	±0.25pF	0.33max		20
15	GRM0335C1H1R5CA01	0603M/0201	COG	50Vdc	1.5pF	±0.25pF	0.33max		20
16	GRM0335C1H1R6CA01	0603M/0201	COG	50Vdc	1.6pF	±0.25pF	0.33max		20
17	GRM0335C1H1R7CA01	0603M/0201	COG	50Vdc	1.7pF	±0.25pF	0.33max		20
18	GRM0335C1H1R8CA01	0603M/0201	COG	50Vdc	1.8pF	±0.25pF	0.33max		20
19	GRM0335C1H1R9CA01	0603M/0201	COG	50Vdc	1.9pF	±0.25pF	0.33max		20
20	GRM0335C1H2R0CA01	0603M/0201	COG	50Vdc	2.0pF	±0.25pF	0.33max		20
21	GRM0335C1H2R1CA01	0603M/0201	COG	50Vdc	2.1pF	±0.25pF	0.33max		20
22	GRM0335C1H2R2CA01	0603M/0201	COG	50Vdc	2.2pF	±0.25pF	0.33max		20
23	GRM0335C1H2R3CA01	0603M/0201	COG	50Vdc	2.3pF	±0.25pF	0.33max		20
24	GRM0335C1H2R4CA01	0603M/0201	COG	50Vdc	2.4pF	±0.25pF	0.33max		20
25	GRM0335C1H2R5CA01	0603M/0201	COG	50Vdc	2.5pF	±0.25pF	0.33max		20
26	GRM0335C1H2R6CA01	0603M/0201	COG	50Vdc	2.6pF	±0.25pF	0.33max		20
27	GRM0335C1H2R7CA01	0603M/0201	COG	50Vdc	2.7pF	±0.25pF	0.33max		20
28	GRM0335C1H2R8CA01	0603M/0201	COG	50Vdc	2.8pF	±0.25pF	0.33max		20
29	GRM0335C1H2R9CA01	0603M/0201	COG	50Vdc	2.9pF	±0.25pF	0.33max		20
30	GRM0335C1H3R0CA01	0603M/0201	COG	50Vdc	3.0pF	±0.25pF	0.33max		20
31	GRM0335C1H3R3CA01	0603M/0201	COG	50Vdc	3.3pF	±0.25pF	0.33max		20
32	GRM0335C1H3R6CA01	0603M/0201	COG	50Vdc	3.6pF	±0.25pF	0.33max		20
33	GRM0335C1H3R9CA01	0603M/0201	COG	50Vdc	3.9pF	±0.25pF	0.33max		20

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
34	GRM0335C1H4R3CA01	0603M/0201	COG	50Vdc	4.3pF	±0.25pF	0.33max		20
35	GRM0335C1H4R7CA01	0603M/0201	COG	50Vdc	4.7pF	±0.25pF	0.33max		20
36	GRM0335C1H5R1CA01	0603M/0201	COG	50Vdc	5.1pF	±0.25pF	0.33max		20
37	GRM0335C1H5R6CA01	0603M/0201	COG	50Vdc	5.6pF	±0.25pF	0.33max		20
38	GRM0335C1H6R2CA01	0603M/0201	COG	50Vdc	6.2pF	±0.25pF	0.33max		20
39	GRM0335C1H6R8CA01	0603M/0201	COG	50Vdc	6.8pF	±0.25pF	0.33max		20
40	GRM0335C1H7R5CA01	0603M/0201	COG	50Vdc	7.5pF	±0.25pF	0.33max		20
41	GRM0335C1H8R2CA01	0603M/0201	COG	50Vdc	8.2pF	±0.25pF	0.33max		20
42	GRM0335C1H9R1CA01	0603M/0201	COG	50Vdc	9.1pF	±0.25pF	0.33max		20
43	GRM0335C1H100JA01	0603M/0201	COG	50Vdc	10pF	±5%	0.33max		20
44	GRM0335C1H120JA01	0603M/0201	COG	50Vdc	12pF	±5%	0.33max		20
45	GRM0335C1H150JA01	0603M/0201	COG	50Vdc	15pF	±5%	0.33max		20
46	GRM0335C1H180JA01	0603M/0201	COG	50Vdc	18pF	±5%	0.33max		20
47	GRM0335C1H220JA01	0603M/0201	COG	50Vdc	22pF	±5%	0.33max		20
48	GRM0335C1H270JA01	0603M/0201	COG	50Vdc	27pF	±5%	0.33max		20
49	GRM0335C1H330JA01	0603M/0201	COG	50Vdc	33pF	±5%	0.33max		20
50	GRM0335C1H390JA01	0603M/0201	COG	50Vdc	39pF	±5%	0.33max		20
51	GRM0335C1H470JA01	0603M/0201	COG	50Vdc	47pF	±5%	0.33max		20
52	GRM0335C1H560JA01	0603M/0201	COG	50Vdc	56pF	±5%	0.33max		20
53	GRM0335C1H680JA01	0603M/0201	COG	50Vdc	68pF	±5%	0.33max		20
54	GRM0335C1H820JA01	0603M/0201	COG	50Vdc	82pF	±5%	0.33max		20
55	GRM0335C1H101JA01	0603M/0201	COG	50Vdc	100pF	±5%	0.33max		100
56	GRM0335C1H121JA01	0603M/0201	COG	50Vdc	120pF	±5%	0.33max		20
57	GRM0335C1H151JA01	0603M/0201	COG	50Vdc	150pF	±5%	0.33max		20
58	GRM0335C1H181JA01	0603M/0201	COG	50Vdc	180pF	±5%	0.33max		20
59	GRM0335C1H221JA01	0603M/0201	COG	50Vdc	220pF	±5%	0.33max		20
60	GRM0335C1E271JA01	0603M/0201	COG	25Vdc	270pF	±5%	0.33max		20
61	GRM0335C1E331JA01	0603M/0201	COG	25Vdc	330pF	±5%	0.33max		20
62	GRM0335C1E391JA01	0603M/0201	COG	25Vdc	390pF	±5%	0.33max		20
63	GRM0335C1E471JA01	0603M/0201	COG	25Vdc	470pF	±5%	0.33max		20
64	GRM0335C1E561JA01	0603M/0201	COG	25Vdc	560pF	±5%	0.33max		20
65	GRM0335C1E681JA01	0603M/0201	COG	25Vdc	680pF	±5%	0.33max		20
66	GRM0335C1E821JA01	0603M/0201	COG	25Vdc	820pF	±5%	0.33max		20
67	GRM0335C1E102JA01	0603M/0201	COG	25Vdc	1000pF	±5%	0.33max		20