

Part Details:-

Part Number	Description
GRM03-X5R-X6S-X7R-KIT-DE	0201 CLASS 2 CAPACITOR ASSORTMENT KIT

KIT Contents:-

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
1	GRM033R71E101KA01	0603M/0201	X7R	25Vdc	100pF	±10%	0.33max		20
2	GRM033R71E151KA01	0603M/0201	X7R	25Vdc	150pF	±10%	0.33max		20
3	GRM033R71E221KA01	0603M/0201	X7R	25Vdc	220pF	±10%	0.33max		20
4	GRM033R71E331KA01	0603M/0201	X7R	25Vdc	330pF	±10%	0.33max		20
5	GRM033R71E471KA01	0603M/0201	X7R	25Vdc	470pF	±10%	0.33max		20
6	GRM033R71E681KA01	0603M/0201	X7R	25Vdc	680pF	±10%	0.33max		20
7	GRM033R71E102KA01	0603M/0201	X7R	25Vdc	1000pF	±10%	0.33max		20
8	GRM033R71E152KA01	0603M/0201	X7R	25Vdc	1500pF	±10%	0.33max		20
9	GRM033R71E222KA12	0603M/0201	X7R	25Vdc	2200pF	±10%	0.33max		20
10	GRM033R71E332KA12	0603M/0201	X7R	25Vdc	3300pF	±10%	0.33max		20
11	GRM033R71E472KE14	0603M/0201	X7R	25Vdc	4700pF	±10%	0.33max		20
12	GRM033R71E682KE14	0603M/0201	X7R	25Vdc	6800pF	±10%	0.33max		20
13	GRM033R71E103KE14	0603M/0201	X7R	25Vdc	0.01μF	±10%	0.33max		100
14	GRM033R61C153KE84	0603M/0201	X5R	16Vdc	0.015μF	±10%	0.33max		20
15	GRM033R61C223KE84	0603M/0201	X5R	16Vdc	0.022μF	±10%	0.33max		20
16	GRM033R61C333KE84	0603M/0201	X5R	16Vdc	0.033μF	±10%	0.33max		20
17	GRM033R61C473KE84	0603M/0201	X5R	16Vdc	0.047μF	±10%	0.33max		20
18	GRM033R61C683KE84	0603M/0201	X5R	16Vdc	0.068μF	±10%	0.33max		20
19	GRM033R61C104KE14	0603M/0201	X5R	16Vdc	0.1μF	±10%	0.33max		20
20	GRM033R61C224KE14	0603M/0201	X5R	16Vdc	0.22μF	±10%	0.33max		20
21	GRM033C71C104KE14	0603M/0201	X7S	16Vdc	0.1μF	±10%	0.33max		20
22	GRM033C80J224KE90	0603M/0201	X6S	6.3Vdc	0.22μF	±10%	0.33max		20
23	GRM033R60J474KE90	0603M/0201	X5R	6.3Vdc	0.47μF	±10%	0.33max		20
24	GRM033R60J105MEA2	0603M/0201	X5R	6.3Vdc	1μF	±20%	0.35max		100
25	GRM033R60J225ME47	0603M/0201	X5R	6.3Vdc	2.2μF	±20%	0.39max		100
26	GRM035R60J475ME15	0603M/0201	X5R	6.3Vdc	4.7μF	±20%	0.55max		100