

RBV3000CESV | 3000W Electric Blower Vac, Over/Under Style



- Powerful 3000W motor.
- 3-in-1 blower and vacuum can be used as blower only, vacuum only, or with both tubes on the the tool.
- Multi-speed dial provides maximum airflow speed of 375km/h with quiet mode.
- Ultimate blower performance with 16 m³/min air volume.
- PowerMulching™ heavy duty metal blade offers 16:1 mulching ratio for better composting.
- Quick-change lever to switch between blow and vacuum mode.
- Vertebrae™ shoulder strap provides maximum comfort to the user and balances the tool.

	RBV3000CESV
Air volume (m ³ per minute)	16
Airflow speed (km/h)	375
Collection bag capacity (l)	45
Mulching ratio	16:1
Power	3000W
Sound Power [dB Lwa]	106.6
Sound power level [dB[A]]	108
Sound power level guaranteed [dB[A]]	110
Sound power level uncertainty [dB[A]]	2
Sound pressure level (dB(A))	92.5
Sound pressure level uncertainty [dB[A]]	2
Supplied in	Recyclable Carton
Variable speed	Yes
Vibration level [m/s ²]	4.6
Vibration Level Auxiliary Handle [m/s ²]	4.0
Vibration Level Main Handle [m/s ²]	6.8
Vibration uncertainty [m/s ²]	1.5
Weight (kg)	5.1