

RMT1801M | 18V Cordless Multi Tool



- A versatile multi-purpose tool with both sanding and cutting heads.
- Quick change attachments for hassle free transition between sanding and sawing.
- LED lights up your work area for better visibility.
- Variable speed for ultimate control across a range of applications.
- Universal accessory adaptor makes the product compatible with any brand of accessories.

	RMT1801M
Battery pack capacity (Ah)	-
Battery type	-
Charger included?	No
No. of batteries supplied	0
Oscillation angle	3°
Oscillation rate (opm)	0-20000
Power	18V
Sound power level [dB(A)]	96.0
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (dB(A))	85.0
Sound pressure level uncertainty [dB(A)]	3.0
Supplied in	Recyclable Carton
Vibration cutting metal [m/s ²]	5.7
Vibration cutting metal uncertainty [m/s ²]	1.5
Vibration cutting wood [m/s ²]	4.2
Vibration cutting wood uncertainty [m/s ²]	1.5
Vibration sanding (m/s ²)	1.4
Vibration sanding uncertainty [m/s ²]	1.5
Weight [without battery] [Kg]	1.1
Weight with battery pack (kg)	1.5