

## RAD1801M | 18V Cordless Right Angle Drill



- Cordless right angle drill ideal for drilling in wood and metal or driving screws in tight spaces.
- Keyless chuck for quick and easy bit changes.
- LED lights up your work area for better visibility.
- Magnetic drill bit tray for easy storage and access to your drill bits.

	RAD1801M
Battery pack capacity (Ah)	-
Battery type	-
Charger included?	No
Charging time	-
Chuck capacity (mm)	10
Max drilling steel (mm)	10
Max. drilling wood (mm)	38
Max. torque (Nm)	15
No load speed (rpm)	0-1100
No. of batteries supplied	0
Power	18V
Sound power level [dB(A)]	78.5
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (dB(A))	67.5
Sound pressure level uncertainty [dB(A)]	3.0
Supplied in	Recyclable Carton
Torque settings	-
Vibration drilling into Metal [m/s <sup>2</sup> ]	1.2
Vibration drilling into metal uncertainty [m/s <sup>2</sup> ]	1.5
Vibration screw driving [m/s <sup>2</sup> ]	0.3
Vibration screw driving uncertainty [m/s <sup>2</sup> ]	1.5
Weight [without battery] [Kg]	1.4
Weight with battery pack (kg)	1.8