

## Operating System

Operating System

Windows 10 Pro

## Processor & Chipset

Processor Manufacturer

Intel®

Processor Type

Core™ i3

Processor Model

i3-7100

Processor Core

Dual-core (2 Core™)

Processor Speed

3.90 GHz

64-bit Processing

Yes

Chipset Manufacturer

Intel®

Chipset Model

H110 Express

## Memory

Standard Memory

4 GB

Maximum Memory

32 GB

Memory Technology

DDR4 SDRAM

Memory Technology

DDR4

Standard Memory

4 GB (standard)

Maximum Memory

Up to 32 GB (maximum)

## Storage

Number of Hard Drives

1

Total Hard Drive Capacity

1 TB

Hard Drive Interface

Serial ATA/600

Optical Drive Type

DVD-Writer

Optical Media Supported

DVD-RAM/±R/±RW

Hard Drive Capacity

1 TB hard drive

Optical Drive Type

DVD-Writer

## Display & Graphics

Graphics Controller Manufacturer

Intel®

Graphics Controller Model

HD Graphics 630

Graphics Memory Technology

DDR4 SDRAM

Graphics Memory Accessibility

Shared

## Network & Communication

Ethernet Technology

Gigabit Ethernet

## I/O Expansions

Number of Total Expansion Slots

1

Number of PCI Express x16 Slots

1

## Interfaces/Ports

HDMI

Yes

Number of USB 2.0 Ports

4

Number of USB 3.1 Gen 1 Ports

2

Total Number of USB Ports

6

Network (RJ-45)

Yes

Audio Line In

Yes

Audio Line Out

Yes

VGA

Yes

## Software

Operating System

Windows 10 Pro

Operating System Architecture

64-bit

## Power Description

Maximum Power Supply Wattage

220 W

## Physical Characteristics

Height

340 mm

Width

165 mm

Depth

320 mm

## Miscellaneous

Environmentally Friendly

Yes

Environmental Certification

RoHS

## Warranty

Warranty

Standard Warranty.