

Strain Relief Deluxe Cord Grips

Aluminum Fittings, Stainless Steel Mesh, Liquidtight, for Insulated Cables




Read This Data

It is important that you read all breaking strength, safety and technical data relating to this product on pages T-68 through T-74.



Straight Male



Straight Male Thread

Grip Diameter Range Inches (cm)	Thread Size N.P.T. (Inches)	Form Size	Catalog Numbers
.250"-.312" (.63-.79)	3/8"	F1	07401001
.312"-.375" (.79-.95)			07401002
.375"-.437" (.95-1.11)			07401003
.187"-.250" (.47-.63)	1/2"	F2	07401004
.250"-.375" (.63-.95)			07401006
.375"-.500" (.95-1.27)			07401008
.500"-.625" (1.27-1.59)			07401010
.625"-.750" (1.59-1.90)	1/2"	F3	074011247*
.750"-.875" (1.90-2.22)			074011248*
.187"-.250" (.47-.63)	3/4"	F2	07401011
.250"-.375" (.63-.95)			07401013
.375"-.500" (.95-1.27)			07401015
.500"-.625" (1.27-1.59)			07401017
.625"-.750" (1.59-1.90)	3/4"	F3	07401018
.750"-.875" (1.90-2.22)			074011249*
.375"-.500" (.95-1.27)	1"	F4	074011195
.500"-.625" (1.27-1.59)			07401019
.625"-.750" (1.59-1.90)			07401021
.750"-.875" (1.90-2.22)			07401023
.875"-1.000" (2.22-2.54)			07401025
1.000"-1.125" (2.54-2.86)			074011250*
1.125"-1.250" (2.86-3.17)			074011028*
1.250"-1.375" (3.17-3.49)			074011029*
.750"-.875" (1.90-2.22)	1 1/4"	F5	074011251
.875"-1.000" (2.22-2.54)			07401026
1.000"-1.125" (2.54-2.86)			07401027
1.125"-1.250" (2.86-3.17)			07401028
1.250"-1.375" (3.17-3.49)			074011178*
.750"-.875" (1.90-2.22)			074011252
.875"-1.000" (2.22-2.54)			07401029
1.000"-1.125" (2.54-2.86)			07401030
1.125"-1.250" (2.86-3.17)	1 1/2"	F5	07401031
1.250"-1.375" (3.17-3.49)			07401032
1.312"-1.437" (3.33-3.65)			074011253
1.437"-1.562" (3.65-3.97)			074011254*
1.562"-1.687" (3.97-4.28)			074011255*
1.687"-1.812" (4.28-4.60)	1 1/2"	F6	074011256*
1.750"-1.875" (4.44-4.76)			074011257*
1.250"-1.375" (3.17-3.49)			074011258
1.312"-1.437" (3.33-3.65)			074011259
1.437"-1.562" (3.65-3.97)			07401033
1.562"-1.687" (3.97-4.28)	2"	F6	07401034
1.687"-1.812" (4.28-4.60)			07401035
1.750"-1.875" (4.44-4.76)			074011260
1.812"-1.937" (4.60-4.92)			074011261
1.937"-2.062" (4.92-5.24)			074011262*
2.062"-2.187" (5.24-5.55)	2"	F7	074011263*
2.187"-2.312" (5.55-5.87)			074011264*
2.312"-2.437" (5.87-6.19)			074011265*
1.688"-1.812" (4.29-4.60)			074011030
1.812"-1.937" (4.60-4.92)			074011031
1.937"-2.062" (4.92-5.24)	2 1/2"	F7	074011032
2.062"-2.187" (5.24-5.55)			074011033
2.187"-2.312" (5.55-5.87)			074011034
2.312"-2.437" (5.87-6.19)			074011266*
1.937"-2.062" (4.92-5.24)			3"
2.062"-2.187" (5.24-5.55)	074011037		
2.187"-2.312" (5.55-5.87)	074011038		
2.312"-2.437" (5.87-6.19)	074011039		
2.437"-2.625" (6.19-6.67)	074011186		
2.625"-2.812" (6.67-7.14)	3"	F8	074011187
2.812"-3.000" (7.14-7.62)			074011188
3.000"-3.250" (7.62-8.25)			074011189*

*Cable jacket may have to be stripped to pass through connector body.

Kellems® Deluxe Cord Grips are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 of the National Electric Code Sections 501-4(b), 502-4(a), 502-4(b), 503-3(a) and 503 3(b).