



2456-21

M12™ Cordless 1/4" Lithium-Ion Ratchet Kit



Choose the sub-compact ratchet with best-in-class power, speed and durability. The M12™ Cordless 1/4" Lithium-Ion Ratchet is the ideal tool for auto mechanics, maintenance and repair professionals looking for maximum performance and productivity in a subcompact cordless tool. It utilizes a powerful 12-volt motor to produce up to 30 ft-lbs of torque and 250 RPM, giving users the power and speed of a pneumatic ratchet without the airhose. It's powered by the M12 REDLITHIUM™ Battery Pack, which delivers more work per charge and more work over pack life than the competitors, as well as best-in-class performance in extreme jobsite conditions. At just 10-3/4" long and 1.9 lbs, the ratchet is tool-belt portable, and features a 3/4" low-profile head design for work in the tightest of spaces and engine bays. The variable-speed metal trigger and reinforced steel housing provide maximum control and durability with any application. The kit includes one M12 battery, a 30-minute charger and carrying case.

INCLUDES:

- (1) M12™ Cordless 1/4" Ratchet (Tool Only) (2456-20)
- (1) M12™ Lithium-ion Battery Charger (48-59-2401)
- (1) M12™ REDLITHIUM™ CP1.5 Battery Pack (48-11-2401)
- (1) Carrying Case

- ✓ Powerful 12-volt motor: Delivers up to 30 ft-lbs of torque
- ✓ REDLITHIUM™ Battery Technology: Superior pack construction, electronics, and performance deliver more work per charge and more work over pack life than any battery on the market
- ✓ On-board fuel gauge: Helps you monitor the charge precisely for less downtime on the job
- ✓ Superior fastening speed: Produces 250 RPM, with variable-speed trigger for greater control
- ✓ REDLINK™ Intelligence: Provides optimized performance and overload protection using total system communication between tool, battery and charger
- ✓ Built-in LED light: Illuminates work surfaces in dark locations

BATTERY SPECIFICATIONS

| | |
|---------|-----|
| Voltage | 12V |
|---------|-----|

PRODUCT SPECIFICATIONS

| | |
|----------------|-------------------------|
| Battery System | M12 |
| Length | 10-3/4" |
| Warranty | 5 Year Limited Warranty |

| | |
|---------------|-----------|
| Peak Torque | 30 ft-lbs |
| No Load Speed | 0-250 RPM |
| Power Source | Cordless |