

Swivel/Tilt Wall Mount for 37" to 70" TVs and Monitors

MODEL NUMBER: **DWM3770X**



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

Description

The VESA-compliant DWM3770X Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 37 to 70 inches.

The articulating arm has six pivots that adjust independently for angle to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 120° swivel, -15° to +15° tilt and -3° to +3° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with scratch-resistant powder-coated finish supports up to 165 pounds. Mounting hardware included. Built-in bubble level allows accurate display leveling. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm and 600 x 400 mm.

Features

Mounts Your TV or Monitor to the Wall

- Fits most flat-panel televisions, monitors and other displays from 37 to 70 in.
- Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants
- Articulated arm with 6 pivots adjusts independently for angle
- Mounting hardware included

Convenient One-Touch Adjustment

- 120° swivel, -15° to +15° tilt and -3° to +3° screen level adjustment capability provides comfortable

Highlights

- Fits most flat-panel displays from 37 to 70 in.
- One-touch adjustment for comfortable viewing
- 120° swivel, -15° to +15° tilt and -3° to +3° screen adjustment
- Supports up to 165 lb.

Package Includes

- Wall mount
- Mounting template
- (2) Adapter brackets
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual



viewing from multiple angles

Durable Metal Construction

- Supports up to 165 lb.
- Scratch-resistant powder-coated finish blends with any décor
- Built-in bubble level allows accurate display leveling

VESA Compliance

- Supports the following VESA mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm and 600 x 400 mm

Specifications

OVERVIEW	
UPC Code	037332187437
PHYSICAL	
Mounting Location	Wall
Shipping Dimensions (hwd / in.)	4.40 x 9.50 x 27.90
Shipping Dimensions (hwd / cm)	11.18 x 24.13 x 70.87
Shipping Weight (lbs.)	20.60
Shipping Weight (kg)	9.34
Unit Dimensions (hwd / in.)	17.32 x 23.62 x 20.62
Unit Dimensions (hwd / cm)	44.0 x 60.1 x 52.4
Unit Weight (lbs.)	17.38
Unit Weight (kg)	7.88
Material of Construction	Steel
Color	Black
Screen Size Compatibility (in.)	37 - 70
Screen Size Compatibility (cm)	94.1 - 178.0
VESA Pattern (mm)	200x200; 300x300; 400x200; 400x400; 600x400
Motion	Full
Degrees of Motion	-15/+15 Tilt, 120 Swivel, -3/+3 Level Adjustment
Min/Max Arm Extension (in.)	4.57 min to 20.63 max
Min/Max Arm Extension (cm)	116 min to 524 max
Maximum Weight Capacity (lbs.)	165



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Maximum Weight Capacity (kg)	75
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>