



## Specification

### CP301 110V 16A CT Industrial Check Plug



#### Electrical

Operating voltage range: 110V AC rms  
(55V-0-55V centre tapped only)  
Frequency response: 30Hz to 70Hz  
Power consumption: <0.9W  
Power: from mains socket under test

#### General

Plug type: yellow, 16A/32A, 3-pin plug to BS  
EN 60309 (BS 4343)  
Dimensions: 65 x 65 x 47mm (check plug  
body)  
Weight: approx. 195g

#### Environmental

Temperature (Operating & Storage): -10°C to 40°C, at max. 60% RH  
Altitude: up to 2000m  
Pollution degree 2

#### Safety

Conforms to BS EN 61010-1, CAT II 150V  
Class II, double insulation

#### EMC

Conforms to BS EN 61326-1

## Check out what else you can get from Martindale:

- 18th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited  
Metrohm House, Penfold Trading Estate, Imperial Way, Watford WD24 4YY, UK  
Tel: +44 (0)1923 441717 Fax: +44 (0)1923 446900  
E-mail: sales@martindale-electric.co.uk  
Website: www.martindale-electric.co.uk



© 2016 Martindale Electric Company Ltd.  
Registered in England No. 3387451. Rev 3 LITCP301