

**EM2929 Series  
EuroMag Terminal Blocks**

Hi-Current; 10.16 Centers

**SPECIFICATIONS**

**Rating:** 65A, 300V

**Center Spacing:** 0.40" (10.16mm)

**Wire Range:** #6-20 AWG

**Housing Material:** UL rated 94V0 Thermoplastic

**Contact Material:** Tin-Plated Copper

**Cage Material:** Steel, Chromate Plated

**Screw Size:** M4 Stainless Steel

**Operating Temperature:** 105°C (221°F) max., -40°C (-40°F) min.

**Torque Rating:** 15 lb-in.

**Recommended PCB Hole Diameters:** 0.055" (1.40mm)

**Construction:** Mold to length

**Agency Information:** File E62622; CE Certified




EM292908

**Dimensions - mm**

Poles	L (mm)
2	20.34
3	30.50
4	40.66
5	50.82
6	60.98
7	71.14
8	81.30

To convert to inches, divide by 25.4



Terminal Blocks:  
Single Row

EuroMag Series  
High Current

Edge Connectors,  
One-Sided Boards

Compliance  
References

**Part Numbering System**

Series

# of Poles

EM2929

□□ - UL

02 to 08