

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2451360620](#)  
**Status:** **Active**  
**Overview:** [Mega-Fit Power Connectors](#)  
**Description:** Mega-Fit-to-Mega-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 2.0m Length, Gold (Au) Plated, 6 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification 2027040017-PK \(PDF\)](#) [Product Literature \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">245136</a>
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mega-Fit-to-Mega-Fit
Overmolded	Yes
Overview	<a href="#">Mega-Fit Power Connectors</a>
Product Literature Order No	987651-4662
Product Name	Mega-Fit OTS
UPC	191128798389

**Physical**

Cable Length	2.0m
Circuits (Loaded)	6
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	PBT
Net Weight	567.800/g
Packaging Type	Bag
Pitch - Mating Interface	5.70mm
Plating min - Mating	0.381µm
Plating min - Termination	0.381µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	12.00mm
Wire Size AWG	12
Wire/Cable Type	UL 2464

**Electrical**

Current - Maximum per Contact	18.0A
Voltage - Maximum	300V AC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2027040017-PK
Sales Drawing	2014400075-000



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[245136](#) Series

**Mates With**

Mega-Fit Header [76825](#) , [76829](#) , [172064](#) ,  
[172065](#)