



PRODUCT #: 880437

## **LEDLENSER iLH8R**

If you're smart you'll err on the side of caution when working in explosive areas of Class 1, Div 2. And if you're really smart, you'll use the rechargeable version of the iLH8. After all it's 10 g lighter but has the same features as the battery powered version: dustproof housing protected against powerful water jets (IP66), comfortable to carry and features our patented Advanced Focus System. All this at a maximum battery life of 40 hours per charge. So the iLH8R is still running at full power when you're feeling drained.

**KEY FEATURES:**

- Rechargeable via charging cradle
- Magnetic Switch for easy operation with gloves and protective equipment
- Patented Advanced Focus System
- Long battery life (up to 40 hours)
- Red rear light as a position marker

**APPROVALS:**

- Class 1, Division 2, Groups A,B,C,D;
- Class II, Division 1, Groups E,F,G; Class III, Temperature Code: T4
- ATEX: II 3G Ex ic IIC T4 Gc, II 3D Ex ic IIIC T135°C Dc



**WEIGHT:** 12.06 oz. | 342 g  
**BATTERY:** Rechargeable li-ion 3.7v

FL1 STANDARD	MAX	MIN
	<b>300</b> LUMENS	<b>50</b> LUMENS
	<b>160m</b>	<b>70m</b>
	<b>7h</b>	<b>40h</b>



**Industry-leading Warranty**

All Ledlenser products come backed by our industry-leading seven-year warranty. For more information about our warranty, please visit [ledlenserusa.com](http://ledlenserusa.com).

**ADDRESS:**  
 Ledlenser USA  
 PO Box 20446  
 Portland, OR 97294

**PHONE:**  
 Local: (503) 408-5301  
 Toll Free: (800) 650-1245

**WEB:**  
[www.ledlenserusa.com](http://www.ledlenserusa.com)