



PRODUCT #: 880435

LEDLENSER iLH8

This Ledlenser makes it easy to brave any explosive work environment. The iLH8 is not only comfortable to wear, it is also the first headlamp for Class 1, Div 2 with the patented Advanced Focus System. This headlamp provides the right light for any situation and absolute safety for short-term explosive atmospheres. So you keep your mind free as well as your hands, leaving you to concentrate fully on your work.

KEY FEATURES:

- Magnetic Switch for easy operation with gloves and protective equipment
- Focusable
- Long battery life (up to 38 hours)
- Dustproof and protected against powerful water jets (IP66)
- Red rear light as a position marker

APPROVALS:

- Class 1, Division 2, Groups A,B,C,D;
- Class II, Division 1, Groups E,F,G; Class III, Temperature Code: T4
- ATEX: II 3G Ex ic IIC T4 Gc, II 3D Ex ic IIIC T135°C Dc



WEIGHT: 12.17 oz. 345 g
BATTERY: 3x alkaline AA

FL1 STANDARD	MAX	MIN
	280 LUMENS	60 LUMENS
	160m	80m
	9h	38h



Industry-leading Warranty

All Ledlenser products come backed by our industry-leading seven-year warranty. For more information about our warranty, please visit ledlenserusa.com.

ADDRESS:

Ledlenser USA
PO Box 20446
Portland, OR 97294

PHONE:

Local: (503) 408-5301
Toll Free: (800) 650-1245

WEB:

www.ledlenserusa.com