


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2012002040](#)
Status: **Active**
Overview: [Spot-On Wire-to-Board Connector System](#)
Description: Spot-On Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, 4 Circuits, Natural

Documents:

| | |
|--|---|
| Drawing (PDF) | Product Specification 2012000000-PS-000 (PDF) |
| Product Specification 2011960000-A00 (PDF) | Packaging Specification 2012009200-200 (PDF) |
| Product Specification 2011960000-A01 (PDF) | RoHS Certificate of Compliance (PDF) |



Series image - Reference only

General

| | |
|----------------|--|
| Product Family | Crimp Housings |
| Series | 201200 |
| Application | Signal, Wire-to-Board |
| Overview | Spot-On Wire-to-Board Connector System |
| Product Name | Spot-On |
| UPC | 191128252140 |

Physical

| | |
|-------------------------------|----------------|
| Circuits (maximum) | 4 |
| Color - Resin | Natural |
| Gender | Receptacle |
| Glow-Wire Capable | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | PBT |
| Net Weight | 567.000/mg |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.00mm |
| Pitch - Termination Interface | 2.00mm |
| Polarized to Mating Part | Yes |
| Temperature Range - Operating | -40° to +105°C |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|---|
| Packaging Specification | 2012009200-200 |
| Product Specification | 2011960000-A00, 2011960000-A01, 2012000000-PS-000 |
| Sales Drawing | 2012002060-SD-000 |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[201200 Series](#)

Mates With

Spot-On Header [201201](#)

Use With

Receptacle Terminal [201195-6000](#)